

SWISS COLOR® PMU DEVICES & ACCESSORIES

HYGIENE CARTRIDGE DESCRIPTION

For the development of our various hygiene cartridges we use only the latest technology, high quality materials and years of experience. We know that each PMU stylist has developed his/her own style over time, therefore a wide range of different hygiene

cartridges is advantageous. The basis of the hygiene cartridges forms a medically approved plastic, the needles are made of stainless steel. The production is kept under constant and independent control in order to ensure superior quality.



1 – NANO NT

It lends itself especially for very fine hair techniques, extra stable thanks to metal tubes.

Ø 0.25 mm

C



1 – NANO (1) & (2)

Suitable for very natural and realistic eyebrow hair technique and extremely thin lines.

Ø 0.20 mm / Ø 0.25 mm

T C S



1 – MICRO

Even finer and more accurate than the 1 hygiene cartridge. Suitable for finest hair and fine, soft lines.

Ø 0.18 mm

T C S



1 – LINER

Suitable for eyebrow hair technique and thin lines.

Ø 0.33 mm

T C S



3 – MICRO

Fine eyeliner and shades for brows. The sensation of pain is reduced to a minimum by 3-needle points. Thin skin is easy to pigment with this needle. Ø 0.18 mm

T C



3 – OUTLINE

Finer needles as 3 hygiene cartridges. Suitable for fine eyeliner, subtle lip shades and lip contours.

Ø 0.25 mm

T C S



3 – LINER

Especially suitable for lip contour shading and firmer lines.

Ø 0.33 mm

T C S



3 – POWER

Dense and thin lines possible. Well-suited for intense eyebrows, eyeliner and lip contour. Power needles carry more color per insertion. Ø 0.33 mm

T C



3 – SLOPED

The slanted needles are always at the same depth in the skin, providing evenly pigmentation for eyeliner, lip and eyebrow. Ø 0.33 mm

T C S



4 – FLAT

It is for large shading areas like lip shading and areola pigmentations.

Ø 0.33 mm

T C S



5 – ROUND

For lip shading, wide contour of the lip, areola pigmentations, corrections and intensive broad eyeliner. Ø 0.33 mm

T C



5 – SHADER

For lips or eyebrow shades or generally full shades.

Ø 0.33 mm

T C S



5 – POWER

Thick and thin lines are possible, suitable for broad eyeliner and for wide lip contour. Power needles carry more color per insertion. Ø 0.33mm

C



5 – MAGNUM

Flat needle system.

For lip shading, areola and hair thickening.

Ø 0.33mm

C S



5 – SLOPED

Due to the 5-fold amplification, the hygiene cartridge is for the lips, and for a wide upper eyeliner.

Ø 0.33mm

C S



7 – ROUND

For areola pigmentation, big lip surfaces and hair thickening.

Ø 0.33mm

T C S



7 – POWER

Density and wide lines possible. For broad - stroked eyeliner, wide lip contour and hair densities.

Ø 0.33mm

C



9 – MAGNUM

Used for areola pigmentation or hair thickening.

Ø 0.33mm

T C S



LIFT MESO METAL

For Lift MESO concept treatment of the face and cleavage. Only use stamping technique.

C



LIFT MESO

For Lift MESO treatments. Stamping and diamond technique.

T C S



LIFT MESO DERMA

For Microneedling treatments and folic stimulation. Stamping and diamond technique. Only for Derma SR8 hand piece.

D



MICRONEEDLING DERMA

For Microneedling treatments and folic stimulation. Only stamping technique. Only for Derma SR8 hand piece.

D